

### 3 DRAWER HANG-ON LOCKER-HEAVY DUTY

MODEL NO: PTB39003

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.





Refer to instruction manual

Wear protective gloves

#### 1. SAFETY

- □ WARNING! Ensure Health & Safety, local authority, and general workshop practice regulations are adhered to when using this locker.
- ✓ Keep the work area clean, uncluttered and ensure there is adequate lighting.
- ✓ Keep the locker clean and tidy in accordance with good workshop practice.
- **DO NOT** use the locker for any purpose other than that for which it is designed.
- **DO NOT** step on the shelves or drawers.
- DO NOT overload the locker.
- DO NOT clean the locker with any solvents which may damage the surfaces or protective coating.


### 2. INTRODUCTION

Hang-On locker suitable for heavy-duty Premier rollcabs. Heavy-duty welded steel construction for strength and durability. Textured powder coat both solvent and rust resistant. Ball bearing drawer slides provide superior performance and carry heavier loads. All drawers have full width sand blasted aluminium 'Lift & Latch' drawer pulls, making easy access while preventing inadvertent opening when box is being moved. Non-slip drawer liners supplied for all drawers. Integral locking system locks all drawers in each unit with the turn of a key. All supplied with 2 keys. Manufactured to the highest levels of construction to withstand the toughest of workshop/garage conditions.

# 3. SPECIFICATION

Model No	PTB39003
Overall size (W x D x H)	390 x 460 x 1390mm
No. of Drawers	
No. of Shelves	2
Weight	41ka

### 4. CONTENTS




ITEM	DESCRIPTION	QTY
1	M6 x 16 C/Sunk Screw	4
2	Hanger	1
3	Magnet	3
4	Connector	1
5	Washer	2
6	M6 x 20 HHB	2
7	Slide Set	3 sets
8	Drawer liner	3
9	Shelf support	8
10	Lock	1
11	Shelf liner	3
12	Neoprene pad spacers	2


# 5. ASSEMBLY


NOTE: Heavy item - get assistance to assemble.

- 5.1. Securely attach hanger (fig.1 item 2) using screws (fig.1 item 1).
- 5.2. Place neoprene pad spacers (5 x 40 x 80) near lower edge of locker. (see fig.2). The spacer pads have adhesive backs to enable fixing.
- 5.3. Attach connector (fig.1 item 4) to the underside of the locker using the bolts and washers (fig.1 items 5 & 6) (see fig.3 and fig.4).
- 5.4. Hang the locker onto the side of the cabinet.
- 5.5. From the underside, adjust the location of the connector to fully engage it with main cabinet (see fig.3 and fig.4). Tighten securely when in correct position.

5.6. To support shelves, insert shelf supports (fig.1 - item 9) at the desired height making sure that all 4 are at the same level (fig.5).











### **ENVIRONMENT PROTECTION**

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.

**Note**: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: Guarantee is 12 months from purchase date, proof of which is required for any claim.

© Jack Sealey Limited Original Language Version PTB39003 Issue 1 21/08/18