

1/2"SQ DRIVE MICROMETER TORQUE WRENCH

MODEL NO: STW400

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



instruction

manual 1. SAFETY

- ✓ Ensure all workshop safety rules, regulations and conditions are complied with when using the torque wrench.
- Maintain the wrench in good condition and replace any damaged or worn parts. Use genuine parts only. Unauthorised parts may be dangerous and will invalidate the warranty.
- ✓ The wrench is a precision tool, DO NOT abuse it.
- ✓ Maintain correct balance and footing. Ensure the floor is not slippery and wear non-slip shoes.
- ✓ Keep children and unauthorised persons away from the working area.
- □ WARNING! DO NOT use the wrench if damaged or thought to be faulty (Contact Service Agent).
- **DO NOT** drop or throw the wrench.
- **DO NOT** use wrench unless you have been instructed in its use by a qualified person.
- DO NOT use any cleaner which might affect the high pressure grease with which the wrench it is packed.
- √ After use adjust to lowest torque setting (but not below), clean and store in a safe, dry, childproof location.

2. INTRODUCTION

Flip reverse Chrome Vanadium steel ratchet head with smooth action mechanism. Scale graduated in Nm and lb.ft. Calibration tolerance in accordance with BS EN ISO 6789-1:2017. Wrenches are individually tested to standards with ±4% accuracy and each wrench is issued with an individually numbered test certificate. Aluminium knurled handle for comfort and control. Supplied in storage case.

3. SPECIFICATION

Model no	STW400
Drive	1/2"Sq
Length	430mm
Range	40-210Nm (29 5-155lb ft)

4. OPERATION

- **4.1.** Hold torque wrench so that required scale foot.pounds or Newton.metres is uppermost and visible.
- **4.2.** Pull collar downwards to adjust torque setting.
- **4.3.** Turn adjusting grip to select torque setting as follows, for a required setting of 56ft.lb:
- 4.4. Turn grip until top edge of grip is level with the 50ft.lb line on the handle scale and the zero graduation on the grip is aligned with the centre line of the handle scale.
 - Rotate handle further, clockwise, until 6.0 graduation on grip is aligned with centre line to give a setting of 50 + 6 = 56ft.lb.
- When tightening the nut/bolt you will feel and hear the wrench mechanism click when the set torque is reached.

 Immediately stop applying force to wrench to avoid overtightening nut/bolt. Wrench will reset ready for next application.

NOTE: If the wrench has not been used for some time, operate it a few times, at a low setting, to ensure all internal parts are coated in grease.

5. RECALIBRATION

5.1. CALIBRATION CHECK

We recommend to ensure continued accuracy the calibration of each wrench should be checked annually, beginning one year after first use. Calibration should also be checked after any impact, over-torquing or other misuse. Contact your Sealey stockist to arrange recalibration

© Jack Sealey Limited Original Language Version STW400 Issue:2 (5) 10/08/22



TORQUE TOOL CALIBRATION CERTIFICATE

Declaration of Conformance

(in accordance with BS EN ISO 6789-1:2017)¹

Test machine type/name	TORQUE TESTER
Test machine serial No.	31401
Test machine calibration date	10/08/2022
Measurement error ²	±1%

Measurement uncertainty	0.20%
Ambient temperature	26°C
Humidity	52%
Test units: (Nm, lbf.ft, etc)	Nm

,	1	Min Torque:	40	Clockwise					
-	L	Max torque:	210						
Test	Test	Tolerance ± 4 % of Test Load			C	ompleted t	test readinį	g^3	
%	Load	Min	Max	1	2	3	4	5	Average
20%	42	40.32	43.68						
60%	126	120.96	131.04						
100%	210	201.60	218.40						

_	Min Torque:		Anti-clockwise						
4	_	Max torque:		(This part 2 to be completed only where applicable)		able)			
Test	Test	Tolerance ± 4	% of Test Load		C	Completed	test readin	g^3	
%	Load	Min	Max	1	2	3	4	5	Average
20%	0	0.00	0.00						
60%	0	0.00	0.00						
100%	0	0.00	0.00	·					

Tool Model Number	STW400
Tool Serial Number	
Tested by (print name)	
Date of test ⁴	

- **Notes:** ¹Testing is in compliance with International Standard procedures, with test equipment calibrated by a laboratory traceable to International Standards.
 - ² Measurement error shall be less than ¼ of the maximum permissible relative deviation of the torque
 - ³ The observed values fall within the maximum permissible deviation (tolerance). For tools with a flexible head, the result is valid only if the measuring axis is perpendicular to the axis of the tool.
 - ⁴This Sealey Declaration of Conformance is issued at the time of manufacture and its validity is open ended until the torque tool is used for the first time. Unless otherwise stipulated, a period of 12 months, or 5,000 cycles, whichever occurs first, may be taken as default values for the interval between calibration checks. This period starts after first use of the torque tool. (BS EN ISO 6789-1:2017, clause 5.3 refers).



ENVIRONMENT PROTECTION

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.

Note: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: This product comes with a lifetime guarantee against manufacturing defects.



Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR 01284 757500 www.sealey.co.uk 🙊 sales@sealey.co.uk